

Product data sheet

Specifications



NEMA Contactor, Type S,
nonreversing, Size 0, 18A, 2 HP at
230 VAC, 1 phase, up to 100 kA, 1
pole, 120 VAC coil, NEMA 4X

8502SBW15V02CP21P22

! Discontinued

Main

Product Type	Contactor
Product Range	8502S
Contactor Type	Non-reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	1P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Sccr	Circuit-breaker 70 A maximum, SCCR: 100 kA at 480 V AC Fuse J 60 A maximum, SCCR: 100 kA at 600 V AC Fuse T 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 60 A maximum, SCCR: 100 kA at 600 V AC
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent push-to-test Green indicator off incandescent push-to-test
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	13.19 in (335 mm)
Width	6.38 in (162 mm)
Depth	7.13 in (181 mm)

Environmental

Enclosure Type	NEMA 4/4X brushed stainless steel
Certifications	UL listed file E78351 CCN NLDX CSA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21203-8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------