

Product data sheet

Characteristics

8502SCG1V03

Non-Reversing Contactor, Size 1, 2-Pole, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 476.00 USD



Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	27 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	1
Height	10 in (254 mm)
Depth	134 mm
Width	5.98 in (152 mm)

Ordering and shipping details

Category 21192 - 8502,36 SC,SD(NOT S*R,T,W)

Discount Schedule	CP1
GTIN	00785901761914
Nbr. of units in pkg.	1
Package weight(Lbs)	6.3600000000000003
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------