


8502SCG2V81C6FF4TX11

Non-Reversing Contactor, Size 1, 3-Pole, NEMA 1 +Options

Price* : 1,736.00 USD



8502SCG2V81C6FF4TX11 has not been replaced.
Please contact your customer care center for more information.

⚠ Discontinued

Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	480 V (primary), 120 V (secondary)
Contacteur Type	Non-reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (ON-OFF)
Pilot Light	No indicator
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	1
Height	15.87 in (403 mm)
Depth	5 in (127 mm)
Width	6.34 in (161 mm)

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	28.71000000000001
Returnability	N

Country of origin	MX
-------------------	----

Contractual warranty

Warranty period	18 months
-----------------	-----------
