


8502SCG2V81F4T11

Non-Reversing Contactor, Size 1, 3-Pole, NEMA 1 +Options



Price* : 1,202.00 USD



8502SCG2V81F4T11 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Contactator
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	480 V (primary), 120 V (secondary)
Contactator Type	Non-reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	1
Height	15.87 in (403 mm)
Depth	5 in (127 mm)
Width	6.34 in (161 mm)

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
----------	------------------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	28.18
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------