

8502SCG3V02AP1S

Non-Reversing Contactor, Size 1, 4-Pole, NEMA 1 +Options



Price* : 1,175.00 USD



8502SCG3V02AP1S has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Separate control circuit
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contactor Type	Non-reversing
Line Rated Current	27 A
Number of Poles	4P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA
NEMA size	1

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1

Package weight(Lbs)	6
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------