

# 8502SCG5V03

## Non-Reversing Contactor, Size 1, 1-Pole, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 432.00 USD



### Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	27 A
Number of Poles	1P
Phase	1 phase
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	1
Height	10 in (254 mm)
Depth	134 mm
Width	5.98 in (152 mm)

### Ordering and shipping details

Category 21192 - 8502,36 SC,SD(NOT S\*R,T,W)

Discount Schedule	CP1
GTIN	00785901312611
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

**Contractual warranty**

Warranty period	18 months
-----------------	-----------