

8502SCT2V03

Non-Reversing Contactor, Size 1, 3-Pole, NEMA 7/9

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 2,163.00 USD



Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 7/9 cast iron type: bolted
Product certifications	CSA UL listed
NEMA size	1
Height	13.27 in (337 mm)
Depth	7.01 in (178 mm)
Width	10.98 in (279 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21202 - 8502,36 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	21.100000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------