


8502SCW11V03C

Non-Reversing Contactor, Size 1, 2-Pole, NEMA 4/4X +Options



Price* : 1,323.00 USD



8502SCW11V03C has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Contactator
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contactor Type	Non-reversing
Line Rated Current	27 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	CSA UL listed
NEMA size	1
Height	13.19 in (335 mm)
Depth	7.13 in (181 mm)
Width	6.38 in (162 mm)

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	35.789999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------