

8502SCW12V02F4TX10

Non-Reversing Contactor, Size 1, 2-Pole, NEMA 4/4X +Options



Price* : 1,571.00 USD



8502SCW12V02F4TX10 has not been replaced. Please contact your customer care center for more information.

Main

| | |
|---------------------------|--|
| Product or component type | Contacteur |
| Type | 8502S |
| Control Circuit Type | Control circuit transformer |
| Control Circuit Voltage | 110 V AC 50 Hz 120 V AC 60 Hz |
| Contactor Type | Non-reversing |
| Line Rated Current | 27 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC |
| System Voltage | 600 V AC |
| Control Units | No control units |
| Pilot Light | No indicator |
| Auxiliary Contacts | 1 NO |
| Control Circuit Fusing | 2 fuses (primary) |
| Electrical connection | Screw clamp terminals |
| Enclosure Type | NEMA 4/4X brushed stainless steel |
| Product certifications | CSA UL listed |
| NEMA size | 1 |
| Height | 373 mm |
| Depth | 7.13 in (181 mm) |
| Width | 321 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 21203 - 8502,36 W/STAINLESS ENCLOSURES |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 41.259999999999998 |
| Returnability | N |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant Will be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|