

Product data sheet

Specifications

SQUARE D



NEMA Contactor, Type S, nonreversing, Size 2, 45A, 7.5 HP at 230 VAC, 1 phase, up to 100 kA, 2 pole, 240VAC coil, NEMA12

8502SDA1V03

! Discontinued

! Discontinued on: Oct 12, 2021

Main

Product Type	Contactor
Product Range	8502S
Contactor Type	Non-reversing

Complementary

Nema Size	2
Rated Current	45 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Horsepower Rating	7.5 HP 230 V AC 3 HP 115 V AC
Sccr	Circuit-breaker 100 A maximum, SCCR: 100 kA at 480 V AC Fuse J 100 A maximum, SCCR: 100 kA at 600 V AC Fuse T 100 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 100 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 100 A maximum, SCCR: 100 kA at 600 V AC
Coil Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	15.98 in (406 mm)
Width	8.15 in (207 mm)
Depth	9.29 in (236 mm)

Environmental

Enclosure Type	NEMA 12 painted sheet steel
Certifications	UL listed file E78351 CCN NLDX CSA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21192-8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Gtin	00785901998891
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------