

8502SGG2V03

Non-Reversing Contactor, Size 5, 3-Pole, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 8,550.00 USD



Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Common control circuit
Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	270 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	75 HP 200 V AC 100 HP 230 V AC 200 HP 460 V AC 200 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	5
Height	1123 mm
Depth	12.8 in (325 mm)
Width	17.2 in (437 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

Category	21194 - 8502,36SG(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	00785901516590
Nbr. of units in pkg.	1
Package weight(Lbs)	30
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------