

Product data sheet

Specifications

SQUARE D



NEMA Contactor, Type S, nonreversing, Size 5, 270A, 200 HP at 575 VAC, 3 phase, up to 100 kA, 3 pole, 240 V coil, NEMA 1

8502SGG2V03A

! Discontinued

Price*: 8,886.00 USD

Main

Product Type	Contactor
Product Range	8502S
Contactor Type	Non-reversing

Complementary

Nema Size	5
Rated Current	270 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	75 HP 200 V AC 100 HP 230 V AC 200 HP 460 V AC 200 HP 575 V AC
Sccr	Circuit-breaker 400 A maximum, SCCR: 100 kA at 480 V AC Fuse J 400 A maximum, SCCR: 100 kA at 600 V AC Fuse T 400 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 400 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 400 A maximum, SCCR: 100 kA at 600 V AC
Coil Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	2 momentary push-buttons (START-STOP)
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	44.21 in (1123 mm)
Width	17.20 in (437 mm)
Depth	12.80 in (325 mm)

Environmental

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL listed file E78351 CCN NLDX CSA
----------------	---------------------------------------

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	30.00 lb(US) (13.608 kg)

Contractual warranty

Warranty	18 months
----------	-----------