

8502SGG2V81CFF4P21R174TX10

Non-Reversing Contactor, Size 5, 3-Pole, NEMA 1 +Options

Price** : 12,168.00 USD



⚠ Discontinued

8502SGG2V81CFF4P21R174TX10 has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Contactor
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	480 V (primary), 120 V (secondary)
Contactor Type	Non-reversing
Current Rating	270 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	75 HP 200 V AC 100 HP 230 V AC 200 HP 460 V AC 200 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent push-to-test
Auxiliary Contacts	1 NO
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA
NEMA size	5
Height	44.21 in (1123 mm)
Depth	12.80 in (325 mm)
Width	17.20 in (437 mm)

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country of origin	US

Contractual warranty

Warranty	18 months
----------	-----------
