

# 8502SHA2V02SX10

Non-Reversing Contactor, Size 6, 3-Pole, NEMA 12 +Options



Price\* : 29,174.00 USD



8502SHA2V02SX10 has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contactor Type	Non-reversing
Line Rated Current	540 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	1 NO
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA UL listed
NEMA size	6
Height	1651 mm
Depth	12.99 in (330 mm)
Width	20.24 in (514 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

Category	21195 - 8502,36 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	40
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------