

8502SHG2V02SY447

Non-Reversing Contactor, Size 6, 3-Pole, NEMA 1 +Options



Price** : 26,132.00 USD



8502SHG2V02SY447 has not been replaced. Please contact your customer care center for more information.

Main

| | |
|---------------------------|--|
| Product or component type | Contactator |
| Type | 8502S |
| Control Circuit Type | Control circuit transformer |
| Control Circuit Voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Contactator Type | Non-reversing |
| Current Rating | 540 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC |
| Maximum Voltage Rating | 600 V AC |
| Control Units | No control units |
| Pilot Light | No indicator |
| Auxiliary Contacts | Without |
| Control Circuit Fusing | 2 fuses (primary) |
| Electrical connection | Screw clamp terminals |
| Enclosure Type | NEMA 1 painted sheet steel |
| Product certifications | CSA UL listed |
| NEMA size | 6 |
| Height | 65.75 in (1670 mm) |
| Depth | 13.15 in (334 mm) |
| Width | 20.24 in (514 mm) |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

| | |
|---------------------|---------------------------|
| Discount Schedule | CP1 |
| Package weight(Lbs) | 204.00 lb(US) (92.533 kg) |
| Returnability | No |
| Country of origin | US |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|