

8502SHG2V06C6P1

Non-Reversing Contactor, Size 6, 3-Pole, NEMA 1 +Options



Price* : 25,842.00 USD



8502SHG2V06C6P1 has not been replaced. Please contact your customer care center for more information.

Main

| | |
|---------------------------|--|
| Product or component type | Contactator |
| Type | 8502S |
| Control Circuit Type | Control circuit transformer |
| Control Circuit Voltage | 440 V AC 50 Hz 480 V AC 60 Hz |
| Contactator Type | Non-reversing |
| Line Rated Current | 540 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC |
| System Voltage | 600 V AC |
| Control Units | Selector switch (ON-OFF) |
| Pilot Light | Red indicator: on type: incandescent |
| Auxiliary Contacts | Without |
| Control Circuit Fusing | 2 fuses (primary) |
| Electrical connection | Screw clamp terminals |
| Enclosure Type | NEMA 1 painted sheet steel |
| Product certifications | UL listed CSA |
| NEMA size | 6 |
| Height | 65.75 in (1670 mm) |
| Depth | 334 mm |
| Width | 20.24 in (514 mm) |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 21195 - 8502,36 SH,SJ(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 20 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant Will not be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|