

8502SHG2V06R172SX11

Non-Reversing Contactor, Size 6, 3-Pole, NEMA 1 +Options

Price* : 26,175.00 USD



⚠ Discontinued

8502SHG2V06R172SX11 has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	540 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed
NEMA size	6
Height	65.75 in (1670 mm)
Depth	334 mm
Width	20.24 in (514 mm)

Ordering and shipping details

Category	21195 - 8502,36 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	204
Returnability	N

Country of origin	MX
-------------------	----

Contractual warranty

Warranty period	18 months
-----------------	-----------
