

8502SHG2V86P1X11

Non-Reversing Contactor, Size 6, 3-Pole, NEMA 1 +Options



Price** : 25,820.00 USD



8502SHG2V86P1X11 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	600 V (primary), 120 V (secondary)
Contacteur Type	Non-reversing
Current Rating	540 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA
NEMA size	6
Height	65.75 in (1670 mm)
Depth	13.15 in (334 mm)
Width	20.24 in (514 mm)

Ordering and shipping details

Discount Schedule	CP1
-------------------	-----

Package weight(Lbs)	204.00 lb(US) (92.533 kg)
Returnability	No
Country of origin	US

Contractual warranty

Warranty	18 months
----------	-----------
