


# 8502SHW2V02CS

Non-Reversing Contactor, Size 6, 3-Pole, NEMA 4/4X +Options



Price\* : 30,464.00 USD



8502SHW2V02CS has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Contactator
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contactator Type	Non-reversing
Line Rated Current	540 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 4 painted sheet steel
Product certifications	UL listed CSA
NEMA size	6
Height	1657 mm
Depth	308 mm
Width	20.24 in (514 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	204
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------