

Product data sheet

Specifications

SQUARE D



NEMA Contactor, Type S, nonreversing, Size 7, 810A, 1 phase, up to 30 kA, 2 pole, 240 VAC coil, NEMA 12

8502SJA1V03

! Discontinued

Main

Product Type	Contactor
Product Range	8502S
Contactor Type	Non-reversing

Complementary

Nema Size	7
Rated Current	810 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Horsepower Rating	Not rated
Sccr	Circuit-breaker 2000 A maximum, SCCR: 30 kA at 480 V AC Fuse J 1500 A maximum, SCCR: 30 kA at 600 V AC Fuse T 1500 A maximum, SCCR: 30 kA at 600 V AC Fuse RK1 1500 A maximum, SCCR: 30 kA at 600 V AC Fuse RK5 1500 A maximum, SCCR: 30 kA at 600 V AC
Coil Voltage	240 V AC 60 Hz 230 V AC 50 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	92.99 in (2362 mm)
Width	34.49 in (876 mm)
Depth	23.50 in (597 mm)

Environmental

Enclosure Type	NEMA 12 painted sheet steel
Certifications	UL listed file E78351 CCN NLDX CSA

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	21195-8502,36 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	230.00 lb(US) (104.326 kg)

Contractual warranty

Warranty	18 months
----------	-----------