

8502SJA2V08

Non-Reversing Contactor, Size 7, 3-Pole, NEMA 12

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 37,719.00 USD



Main

Product or component type	Contacteur
Type	8502S
Control Circuit Type	Control circuit transformer
Control Circuit Voltage	208 V AC 60 Hz
Contacteur Type	Non-reversing
Line Rated Current	810 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	300 HP 230 V AC 600 HP 460 V AC 600 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA UL listed
NEMA size	7
Height	92.99 in (2362 mm)
Depth	23.5 in (597 mm)
Width	876 mm

Ordering and shipping details

Category 21195 - 8502,36 SH,SJ(NOT S*R,T,W)

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	230
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------