

Product data sheet

Specifications



NEMA Contactor, Type S,
nonreversing, Size 7, 810A, 600 HP
at 575 VAC, 3 phase, up to 30 kA, 3
pole, 480 V coil, NEMA 1

8502SJG2V06R172SX11

! Discontinued

! Discontinued on: Dec 8, 2020

Price*: 34,916.00 USD

Main

Product Type	Contactors
Product Range	8502S
Contactors Type	Non-reversing

Complementary

Nema Size	7
Rated Current	810 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	300 HP 230 V AC 600 HP 460 V AC 600 HP 575 V AC
Sccr	Circuit-breaker 2000 A maximum, SCCR: 30 kA at 480 V AC Fuse J 1500 A maximum, SCCR: 30 kA at 600 V AC Fuse T 1500 A maximum, SCCR: 30 kA at 600 V AC Fuse RK1 1500 A maximum, SCCR: 30 kA at 600 V AC Fuse RK5 1500 A maximum, SCCR: 30 kA at 600 V AC
Coil Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	1 NO + 1 NC
Other Equipment	2 fuses (primary)
Terminal Type	Screw clamp terminals
Height	92.99 in (2362 mm)
Width	34.49 in (876 mm)
Depth	23.50 in (597 mm)

Environmental

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL listed file E78351 CCN NLDX CSA
----------------	---------------------------------------

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------