



Price\* : 624.00 USD



8536SAG11V02A3 has not been replaced. Please contact your customer care center for more information.

### Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	9 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (ON-OFF)
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	00

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed NEMA CSA

### Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	6
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period	18 months
-----------------	-----------