

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 00, 2-Pole, Melting Alloy Overload, NEMA 1+Options

8536SAG11V02CP1X11

Price*: 1,272.00 USD

Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	00
Rated Current	9 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO + 1 NC
Terminal Type	Screw clamp terminals
Height	10.00 in (254 mm)
Width	5.98 in (152 mm)
Depth	5.55 in (141 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA UL Listed NEMA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	7.00 lb(US) (3.175 kg)

Contractual warranty

Warranty	18 months
----------	-----------