

Product data sheet

Characteristics

8536SAG11V02CS

Non-Reversing Starter Size 00, 2-Pole, Melting Alloy Overload, NEMA 1+Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 755.00 USD



Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	9 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	00
Height	10 in (254 mm)
Depth	5.55 in (141 mm)
Width	5.98 in (152 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	6
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------