


8536SAG11V08C6

Non-Reversing Starter Size 00, 2-Pole, Melting Alloy Overload, NEMA 1+Options



Price* : 624.00 USD



8536SAG11V08C6 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	9 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
System Voltage	600 V AC
Control Units	Selector switch (ON-OFF)
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	00

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed NEMA

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	6
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------