


# 8536SAG12V01CP1S

Non-Reversing Starter Size 00, 3-Pole, Melting Alloy Overload, NEMA 1+Options



Price\*\* : 959.00 USD



8536SAG12V01CP1S has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	24 V AC 60 Hz
Motor starter type	Non reversing
Current Rating	9 A
Number of Poles	3P
Number of Phases	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Thermal overload type	Melting alloy 3
Electrical connection	Screw clamp terminals
NEMA size	00

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA NEMA

Ordering and shipping details

Category	21191-8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Package weight(Lbs)	7.00 lb(US) (3.175 kg)
Returnability	No
Country of origin	MX

Contractual warranty

Warranty	18 months
----------	-----------