

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 1,091.00 USD



### Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Current Rating	9 A
Number of Poles	3P
Number of Phases	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Pilot Light	Red indicator on incandescent
Thermal overload type	Melting alloy 3
Electrical connection	Screw clamp terminals
NEMA size	00
Height	10.00 in (254 mm)
Depth	5.55 in (141 mm)
Width	5.98 in (152 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

---

Product certifications	NEMA UL listed CSA
------------------------	--------------------------

---

### Ordering and shipping details

---

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Package weight(Lbs)	3.18 kg (7 lb(US))
Returnability	No
Country of origin	MX

---

### Offer Sustainability

---

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Not compliant

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---