


8536SAG12V02CH20P1SX11

Non-Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR (Class 20)

Price* : 1,337.00 USD



⚠ Discontinued

8536SAG12V02CH20P1SX11 has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	9 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	1 NO + 1 NC
Thermal overload type	Solid state Motor Logic class 20
Electrical connection	Screw clamp terminals
NEMA size	00

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA NEMA

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	6.7800000000000002
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------