

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR (Class 20)

8536SAG12V02CH20SX11

Price\*: 1,002.00 USD

! Discontinued

### Main

|               |               |
|---------------|---------------|
| Product Type  | Starter       |
| Product Range | S             |
| Starter Type  | Non reversing |

### Complementary

|                        |                                                                      |
|------------------------|----------------------------------------------------------------------|
| Nema Size              | 00                                                                   |
| Rated Current          | 9 A                                                                  |
| Number Of Poles        | 3P                                                                   |
| Maximum Voltage Rating | 600 V AC                                                             |
| Phase                  | 3 phase                                                              |
| Type Of Overload       | Solid state Motor Logic class 20                                     |
| Horsepower Rating      | 1.5 HP 200 V AC<br>1.5 HP 230 V AC<br>2 HP 460 V AC<br>2 HP 575 V AC |
| Coil Voltage           | 110 V AC 50 Hz<br>120 V AC 60 Hz                                     |
| Control Circuit Type   | Separate control circuit                                             |
| Control Units          | Selector switch (HAND-OFF-AUTO)                                      |
| Auxiliary Contacts     | 1 NO + 1 NC                                                          |
| Terminal Type          | Screw clamp terminals                                                |

### Environment

|                |                            |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | NEMA<br>CSA<br>UL Listed   |

### Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |
| Country Of Origin | US  |

### Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months