

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR (Class 20)

8536SAG12V02H20SX11

Price*: 798.00 USD

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	00
Rated Current	9 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 20
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Auxiliary Contacts	1 NO + 1 NC
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA UL Listed NEMA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months