

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 734.00 USD



Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Current Rating	9 A
Number of Poles	3P
Number of Phases	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	No control units
Auxiliary Contacts	1 NO + 1 NC
Thermal overload type	Melting alloy 3
Electrical connection	Screw clamp terminals
NEMA size	00
Height	10.00 in (254 mm)
Depth	5.55 in (141 mm)
Width	5.98 in (152 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

Product certifications	NEMA CSA UL listed
------------------------	--------------------------

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901743088
Package weight(Lbs)	2.72 kg (6 lb(US))
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------