


8536SAG12V06BCP1

Non-Reversing Starter Size 00, 3-Pole, Bi-Metallic
Overload, NEMA 1 +Options



Price* : 1,025.00 USD



8536SAG12V06BCP1 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	9 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Thermal overload type	Ambient compensated bimetallic
Electrical connection	Screw clamp terminals
NEMA size	00

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	7
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------