


# 8536SAG12V08A3H20

Non-Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR (Class 20)



Price\* : 692.00 USD



8536SAG12V08A3H20 has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

## Complementary

Control Circuit Voltage	208 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	9 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (ON-OFF)
Thermal overload type	Solid state Motor Logic class 20
Electrical connection	Screw clamp terminals
NEMA size	00

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed NEMA CSA

## Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
----------	------------------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	8
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

**Contractual warranty**

Warranty period	18 months
-----------------	-----------