

Product data sheet

Specifications



Non-Reversing Starter Size 00, 3-Pole, Melting Alloy Overload, NEMA 1+Options

8536SAG12V08AS

Price*: 626.00 USD

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	00
Rated Current	9 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Coil Voltage	208 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	2 momentary push-buttons (START-STOP)
Terminal Type	Screw clamp terminals
Height	10.00 in (254 mm)
Width	5.98 in (152 mm)
Depth	5.55 in (141 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	NEMA UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	8.00 lb(US) (3.629 kg)

Contractual warranty

Warranty	18 months
----------	-----------