

Product data sheet

Characteristics

8536SAG12V81CF4H20T

Non-Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR (Class 20)

Price* : 1,056.00 USD



8536SAG12V81CF4H20T has not been replaced.
Please contact your customer care center for more information.

⚠ Discontinued

Main

| | |
|---------------------------|-----------------------------|
| Product or component type | Starter |
| Type | S |
| Control Circuit Type | Control circuit transformer |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit |
| Motor starter type | Non reversing |
| Line Rated Current | 9 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC |
| System Voltage | 600 V AC |
| Control Units | Selector switch (HAND-OFF-AUTO) |
| Control Circuit Fusing | 2 fuses (primary) |
| Thermal overload type | Solid state Motor Logic class 20 |
| Electrical connection | Screw clamp terminals |
| NEMA size | 00 |

Environment

| | |
|------------------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Product certifications | CSA NEMA UL listed |

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 21191 - 8502,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |

| | |
|---------------------|----|
| Package weight(Lbs) | 50 |
| Returnability | N |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
