


# 8536SAG12V84F4P1T

Non-Reversing Starter Size 00, 3-Pole, Melting Alloy Overload, NEMA 1+Options



Price\* : 1080.00 USD



8536SAG12V84F4P1T has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Range of product	S
Control circuit	Control circuit transformer

## Complementary

[Uc] control circuit voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	9 A
Poles description	3P
Phase	3 phases
Rated power in HP	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control type	No control units
Local signalling	Red indicator : on type: incandescent
Provided equipment	2 fuses (primary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	00
Height	15.87 in (403 mm)
Depth	5.2 in (132 mm)
Width	6.34 in (161 mm)

## Environment

NEMA degree of protection	NEMA 1 painted sheet steel
---------------------------	----------------------------

Product certifications	CSA UL listed NEMA
------------------------	--------------------------

**Ordering and shipping details**

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	20.400000000000002
Returnability	N

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

**Contractual warranty**

Warranty period	18 months
-----------------	-----------