

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 701.00 USD



### Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Current Rating	9 A
Number of Poles	2P
Number of Phases	1 phase
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
Maximum Voltage Rating	600 V AC
Control Units	No control units
Auxiliary Contacts	1 NO + 1 NC
Thermal overload type	Melting alloy 1
Electrical connection	Screw clamp terminals
NEMA size	00
Height	6.77 in (172 mm)
Depth	4.21 in (107 mm)
Width	4.02 in (102 mm)

### Environment

Enclosure Type	Not rated (open device)
Product certifications	UL listed

CSA  
NEMA

---

### Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Package weight(Lbs)	2.27 kg (5 lb(US))
Returnability	No
Country of origin	MX

---

### Offer Sustainability

EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

---

### Contractual warranty

Warranty	18 months
----------	-----------

---