

Product data sheet

Characteristics

8536SAO12V02H30S

Non-Reversing Starter Size 00, 2-Pole, Motor Logic SSOLR +Options

Product availability : Stock - Normally stocked in distribution facility



Price** : 479.00 USD



Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Current Rating	9 A
Number of Poles	3P
Number of Phases	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	No control units
Thermal overload type	Solid state Motor Logic class 10/20
Electrical connection	Screw clamp terminals
NEMA size	00
Height	6.77 in (172 mm)
Depth	4.21 in (107 mm)
Width	3.23 in (82 mm)

Environment

Enclosure Type	Not rated (open device)
Product certifications	UL listed

NEMA
CSA

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901039679
Package weight(Lbs)	1.75 kg (3.85 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------
