


# 8536SBA2V02AP22S

Non-Reversing Starter Size 0, 3-Pole, Melting Alloy Overload,NEMA 12/3R +Options



Price\* : 1,358.00 USD



8536SBA2V02AP22S has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Pilot Light	Green indicator: off type: incandescent with push-to-test
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0

## Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA NEMA UL listed

## Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	16.949999999999999
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------