


8536SBA2V02H10S

Non-Reversing Starter Size 0, 3-Pole, Motor Logic SSOLR (Class 10), NEMA 12/3R



Price* : 752.00 USD



8536SBA2V02H10S has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Solid state Motor Logic class 10
Electrical connection	Screw clamp terminals
NEMA size	0

Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901904090
Nbr. of units in pkg.	1
Package weight(Lbs)	16.080000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------