

# Product data sheet

## Characteristics

# 8536SBA2V03A

Non-Reversing Starter Size 0, 3-Pole, Melting Alloy Overload,NEMA 12/3R +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,025.00 USD



### Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

### Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA

NEMA  
UL listed

### Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901154563
Nbr. of units in pkg.	1
Package weight(Lbs)	14.65
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------