

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 0, 3-Pole, Melting Alloy Overload,NEMA 12/3R +Options

8536SBA2V03CX10

Discontinued

### Main

|               |               |
|---------------|---------------|
| Product Type  | Starter       |
| Product Range | S             |
| Starter Type  | Non reversing |

### Complementary

|                        |                                                                  |
|------------------------|------------------------------------------------------------------|
| Nema Size              | 0                                                                |
| Rated Current          | 18 A                                                             |
| Number Of Poles        | 3P                                                               |
| Maximum Voltage Rating | 600 V AC                                                         |
| Phase                  | 3 phase                                                          |
| Type Of Overload       | Melting alloy 3                                                  |
| Horsepower Rating      | 3 HP 200 V AC<br>3 HP 230 V AC<br>5 HP 460 V AC<br>5 HP 575 V AC |
| Coil Voltage           | 220 V AC 50 Hz<br>240 V AC 60 Hz                                 |
| Control Circuit Type   | Common control circuit                                           |
| Control Units          | Selector switch (HAND-OFF-AUTO)                                  |
| Auxiliary Contacts     | 1 NO                                                             |
| Terminal Type          | Screw clamp terminals                                            |
| Height                 | 12.76 in (324 mm)                                                |
| Width                  | 6.38 in (162 mm)                                                 |
| Depth                  | 8.54 in (217 mm)                                                 |

### Environment

|                |                             |
|----------------|-----------------------------|
| Enclosure Type | NEMA 12 painted sheet steel |
| Certifications | NEMA<br>UL Listed<br>CSA    |

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21191-8502,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1                              |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                   |    |
|-------------------|----|
| Returnability     | No |
| Country Of Origin | MX |

### Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type Of Package 1       | PCE                     |
| Number Of Units In Package 1 | 1                       |
| Package 1 Weight             | 14.72 lb(US) (6.677 kg) |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|