

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 0, 3-Pole, Motor Logic SSOLR (Class 10), NEMA 12/3R

8536SBA2V06H10

Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 10
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 12 painted sheet steel
Certifications	UL Listed CSA NEMA

Ordering and shipping details

Category	21191-8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	50.00 lb(US) (22.68 kg)

Contractual warranty

Warranty	18 months
----------	-----------