

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 0, 3-Pole, Motor Logic SSOLR (Class 20), NEMA 12/3R

8536SBA2V08H20C

! Discontinued

### Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

### Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 20
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Coil Voltage	208 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Terminal Type	Screw clamp terminals

### Environment

Enclosure Type	NEMA 12 painted sheet steel
Certifications	NEMA UL Listed CSA

### Ordering and shipping details

Category	21191-8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	14.32 lb(US) (6.495 kg)
------------------	-------------------------

## Contractual warranty

Warranty	18 months
----------	-----------