

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 0, 3-Pole, Motor Logic SSOLR (Class 20), NEMA 12/3R

8536SBA2V81CF4H209T

Price*: 1,475.00 USD

! Discontinued

Main

| | |
|---------------|---------------|
| Product Type | Starter |
| Product Range | S |
| Starter Type | Non reversing |

Complementary

| | |
|------------------------|--|
| Nema Size | 0 |
| Rated Current | 18 A |
| Number Of Poles | 3P |
| Maximum Voltage Rating | 600 V AC |
| Phase | 3 phase |
| Type Of Overload | Solid state Motor Logic class 20 |
| Horsepower Rating | 3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC |
| Coil Voltage | 120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit |
| Control Circuit Type | Control circuit transformer |
| Control Units | Selector switch (HAND-OFF-AUTO) |
| Other Equipment | 2 fuses (primary) |
| Terminal Type | Screw clamp terminals |

Environment

| | |
|----------------|-----------------------------|
| Enclosure Type | NEMA 12 painted sheet steel |
| Certifications | CSA UL Listed NEMA |

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

