

8536SBA2V81CFF4H20TX11

Non-Reversing Starter Size 0, 3-Pole, Motor Logic
SSOLR (Class 20), NEMA 12/3R

Price* : 2,100.00 USD



⚠ Discontinued

8536SBA2V81CFF4H20TX11 has not been replaced.
Please contact your customer care center for more information.

Main

| | |
|---------------------------|-----------------------------|
| Product or component type | Starter |
| Type | S |
| Control Circuit Type | Control circuit transformer |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit |
| Motor starter type | Non reversing |
| Line Rated Current | 18 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC |
| System Voltage | 600 V AC |
| Control Units | Selector switch (HAND-OFF-AUTO) |
| Auxiliary Contacts | 1 NO + 1 NC |
| Control Circuit Fusing | 2 fuses (primary), 1 fuse (secondary) |
| Thermal overload type | Solid state Motor Logic class 20 |
| Electrical connection | Screw clamp terminals |
| NEMA size | 0 |

Environment

| | |
|------------------------|-----------------------------|
| Enclosure Type | NEMA 12 painted sheet steel |
| Product certifications | NEMA UL listed CSA |

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 21191 - 8502,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1 |

| | |
|-----------------------|----|
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 50 |
| Returnability | N |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
