

# 8536SBA2V81FF4H21P21T11X20

Non-Reversing Starter Size 0, 3-Pole, Motor Logic  
SSOLR (Class 20), NEMA 12/3R

Price\*\* : 2,556.00 USD



⚠ Discontinued

8536SBA2V81FF4H21P21T11X20 has not been replaced.  
Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

## Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Current Rating	18 A
Number of Poles	3P
Number of Phases	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	Red indicator on incandescent push-to-test
Auxiliary Contacts	2 NO
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Solid state Motor Logic class 20
Electrical connection	Screw clamp terminals
NEMA size	0

## Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA UL listed NEMA

## Ordering and shipping details

Category	21191-8502,36 SA,SB(NOT S*R,T,W)
----------	----------------------------------

---

Discount Schedule	CP1
Returnability	No

---

**Contractual warranty**

---

Warranty	18 months
----------	-----------

---