

# 8536SBA2V83F4F10G51T

Non-Reversing Starter Size 0, 3-Pole, Melting Alloy Overload,NEMA 12/3R +Options

Price\* : 1,772.00 USD



⚠ Discontinued

8536SBA2V83F4F10G51T has not been replaced.  
Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

## Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 24 V AC 60 Hz secondary circuit
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary), 2 fuses (secondary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	13.5 in (343 mm)
Depth	7.99 in (203 mm)
Width	11.89 in (302 mm)

## Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	NEMA CSA UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------