


8536SBA2V84CFF4P1TX10

Non-Reversing Starter Size 0, 3-Pole, Melting Alloy Overload,NEMA 12/3R +Options

Price* : 2213.00 USD



⚠ Discontinued

8536SBA2V84CFF4P1TX10 has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Starter
Range of product	S
Control circuit	Control circuit transformer

Complementary

[Uc] control circuit voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	18 A
Poles description	3P
Phase	3 phases
Rated power in HP	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control type	Selector switch (HAND-OFF-AUTO)
Local signalling	Red indicator : on type: incandescent
Auxiliary contact composition	1 NO
Provided equipment	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0

Environment

NEMA degree of protection	NEMA 12 painted sheet steel
Product certifications	NEMA CSA UL listed

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
----------	------------------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	21.120000000000001
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------